



- high volume production steamer
- · all types of textile dyes
- · low fresh steam consumption
- · reproducible and uniform results
- · excellent colour yields
- · user friendly PLC-control
- · easy to maintain
- free configuration, e.g. 50, 100, 150 200 m content or more
- · upgradable with LS-U units
- available in a 1.85, 2.50 and 3.40 meter width
- stainless steel 304 and 316

## options:

- · ascending batch winder/unwinder
- water softener
- external steamnet connection
- · custom power / frequency

## L-STeaM series

The L-STeaM is a loop-type high volume steam/air fixation unit with integrated steam generator for the fixation of textile dyes.

With temperatures between 100 and  $180\,^{\circ}$ C and dwell times from 2 to 30 minutes, the L-STeaM is suitable for all textile dyes. The L-STeaM allows ageing with saturated steam conditions, with temperatures in the range 100 -  $105\,^{\circ}$ C, is also suitable for high temperature fixation of disperse dyes at 165 -  $180\,^{\circ}$ C and can furthermore be used for hot air fixation of pigment dyes.

The huge forced steam circulation combined with the PLC controlled heating and cooling capabilities, guarantee that the selected temperature is achieved throughout the entire steam chamber with an accuracy of a few tenths of a degree, resulting in an all-over equal and reproducible colour. Regeneration of steam during the forced circulation ensures a low fresh steam consumption.

The L-STeaM consist of a dedicated entry and exit unit which are combined with one or more middle sections. The loop formation and extraction are handled by these dedicated units. The bulk of the fabric is present in the middle section so by adding more units, the total content capacity can be expanded up to several hundred meters.

A PLC enables the full control of the line. During production stops the unit is switched to a standby level thereby decreasing the used energy automatically. The unit can be programmed to be left running unattended and to switch off after production has finished.

The standard workflow is from lorry-to-lorry but can be combined with a roll-to-lorry or lorry-to-roll unit as well.

A central steam supply in the factory can be used to injection superheated pressurized steam into the boiler inside the L-STeaM. The resulting saturated steam is then used instead of electically generated steam.


The L-STeaM series is available in a 1.85, 2.50 and 3.40 meter width and is made of 304 and 316 stainless steel. All necessary components are integrated in the E-STeaM.


The L-STeaM is **(€** marked.






## L-STeaM LS-B and LS-U technical specifications







SETeMa B.V. Dommel 34

5422 VH Gemert, NL

Phone : +31 485 385764 e-mail : info@setema.com web : www.setema.com